
## NOTES:


- 1. MATERIAL:
  HOUSING: STAINLESS STEEL
  LENS: D-ZLaF52LA
- 2. COATING (APPLY ACROSS COATING APERTURE) BBAR (600-1050nm) Rabs <1.0% @ 600 - 1050nm

3. CLEAR APERTURE: 5.00 mm

4. RoHS: COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

## **Edmund Optics®**

THIRD ANGLE PROJECTION	$\phi$	TITLE	633nm Alignment, 0.40 NA Fiber Collin w/ FC/APC Connector	nator
ALL DIMS IN	mm	DWG NO	13554	SHEET 1 OF 1

