

NOTES:

 COATING (APPLY ACROSS COATING APERTURE)
ULTRAFAST ENHANCED SILVER R(AVG) > 99% @ 600 - 1000nm @ 0° AOI Rs > 99% @ 540 - 1000nm @ 45° AOI Rp > 98.5% @ 730 - 870nm @ 45° AOI

DAMAGE THRESHOLD, PULSED: 0.3 J/cm² @ 800nm, 48fs, 1 PULSE (TYPICAL) 0.16 J/cm² @ 800nm, 48fs, 100Hz, 1000 PULSES (TYPICAL)





SECTION A-A

PARTS TO THIS DRAWING REFERENCE ONLY

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR

	Edmund Optics®
	Infinite Conjugate Illtrafast Enhanced Silver

THIRD ANGLE_ PROJECTION	$\phi \Box$	TITLE	Infinite Conjugate, Ultrafast Enhanced 15X/0.28NA ReflX Objective	Silver,
ALL DIMS IN	mm	DWG NO	13410	SHEET 1 OF 1