



NOTES:

- 1. COATING:
S1: SPECTRAL BLACK™
THICKNESS: 3 - 7 (µm)
- 2. ABSORBANCE: 99.5 - 99.7 (0 - 10° AOI) %
- 3. ABRASION RESISTANCE: MODERATE
- 4. HUMIDITY RESISTANCE: MIL-C-48497A
- 5. OPERATING TEMPERATURE (°C): -40 to 121
- 6. WAVELENGTH RANGE(µm): 0.3 - 14



DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	Spectral Black Adhesive Foil Sheet 200 x 200mm	
ALL DIMS IN	mm	DWG NO	14727	SHEET 1 OF 1