


Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


750nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

750nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


800nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


800nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


850nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

850nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


900nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


900nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


950nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


950nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


1000nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


1000nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


1050nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


1050nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

1100nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


1100nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


400nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


400nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


450nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


450nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


500nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


500nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


550nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


550nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

600nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY




Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE


600nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


650nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe


650nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

700nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY



Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

COATING CURVE

700nm Techspec® Shortpass Filter: OD >4.0 Coating Performance FOR REFERENCE ONLY

