




NOTES:

- 1. SUBSTRATE MATERIAL:
FLOAT GLASS
- 2. COATING (APFLOW ACROSS CLEAR APERTURE):
S1: ALUMINUM
S2: NONE
- 3. WAVELENGTH RANGE: 250 - 900nm
NOMINAL BLAZE WAVELENGTH: 450nm
GROOVE DENSITY:1800 GROOVES/mm

4. EDGES GROUND

- 5. RoHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION		TITLE		1800 GROOVES, 30x30mm, 250-900nm HOLOGRAPHIC HIGH PERFORMANCE REFLECTION GRATING	
SHAPE	S1 PLANO	S2 PLANO	DWG NO	15753	SHEET 1 OF 1
CLEAR APERTURE	27.0 x 27.0	27.0 x 27.0	ALL DIMS IN	mm	