




NOTES:

1. SUBSTRATE:
N-BK7
2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: R(ABS) <0.25% @ 532nm
R(ABS) <0.25% @ 1064nm
R(AVG) <1.0% @ 500 - 1100nm

4. FINE GRIND SURFACE


5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | S1 | S2 |
|-----------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 60-40 | 60-40 |
| CLEAR APERTURE | 11.25 x 11.25 | 11.25 x 11.25 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |



EO® Edmund Optics®

| | | | |
|--------|----------------------------------------------------------|-------|--------|
| TITLE | 12.5mm SQ., 3mm THICK, YAG-BBAR COATED, λ/4 N-BK7 WINDOW | | |
| DWG NO | 13313 | SHEET | 1 OF 1 |