






- NOTES:
- 1. RoHS: COMPLIANT
 - 2. DAMAGE THRESHOLD:
PULSED LIDT: $1.0 \text{ J/cm}^2 * (\tau/[\text{ns}])^{0.40}$
CW LIDT: 1.0 MW/cm^2
 - 3. GROUP DELAY DISPERSION: 8490 fs^2



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	170mm, 355nm JENar™ Silverline™ F-Theta Scanning Lens
ALL DIMS IN	mm	DWG NO	16771
			SHEET 1 OF 1