

NOTES:




1. RoHS: COMPLIANT

2. DAMAGE THRESHOLD:

PULSED LIDT: $2.5 \text{ J/cm}^2 * (\tau/[\text{ns}])^{0.35}$

CW LIDT: 2.5 MW/cm^2


3. GROUP DELAY DISPERSION: 14700 fs^2



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	108mm, 515-540nm JENar™ F-Theta Scanning Lens	
ALL DIMS IN	mm	DWG NO	17023	SHEET 1 OF 1