

NOTES:




1. RoHS: COMPLIANT

2. DAMAGE THRESHOLD:

PULSED LIDT: $1.0 \text{ J/cm}^2 * (\tau/[\text{ns}])^{0.40}$

CW LIDT: 1.0 MW/cm^2

3. GROUP DELAY DISPERSION: 5260 fs^2



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

Edmund Optics®

THIRD ANGLE PROJECTION		TITLE			510mm, 355nm JENar™ Silverline™ F-Theta Scanning Lens	
		ALL DIMS IN	mm	DWG NO	17026	SHEET 1 OF 1