



- NOTES:
- 1. COATING:
S1: METAL VELVET™
THICKNESS: 5 - 7 (µm)
 - 2. ABSORBANCE: 99.9 (0 - 10° AOI) %
 - 3. ABRASION RESISTANCE: LIGHT, DO NOT TOUCH
 - 4. HUMIDITY RESISTANCE: MIL-C-48497A
 - 5. OPERATING TEMPERATURE (°C): -40 TO +150
 - 6. WAVELENGTH RANGE (µm): 0.3 - 14




DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	20 x 20cm Sheet of Metal Velvet Foil, Low Outgassing Adhesive	
ALL DIMS IN	mm	DWG NO	20053	SHEET 1 OF 1