NOTES:

1. SUBSTRATE: Fused Silica (Corning 7980)

2. ROHS: COMPLIANT


3. SURFACE \$2 TO BE PARALLEL TO SURFACE \$1 TO WITHIN <5 ARCMIN


4. COATING (APPLY ACROSS CLEAR APERTURE)


\$1&\$2: R(AVG) ≤0.4% @ 425 - 675nm

5. TRANSMITTED WAVEFRONT DISTORTION: ≤ 1λ









## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

 S1
 S2

 SHAPE
 PLANO
 PLANO

 SURFACE QUALITY
 60-40
 60-40

 CLEAR APERTURE
 Ø 45.00
 Ø 45.00

 BEVEL
 PROTECTED AS NEEDED
 PROTECTED AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®
 50mm Dia 3mm Thick VIS 0° Coated 1)

HIRD ANGLE ROJECTION		TITLE	50mm Dia., 3mm Thick VIS 0° Coated, 1λ Fused Silica Window	
all DIMS IN	mm	DWG NO	19890	SHEET 1 OF 1