




MOUNTING SLOTS COMPATIBLE WITH  
BREADBOARDS WITH 50mm OR 2in  
HOLE SPACING




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

THIRD ANGLE  
PROJECTION



TITLE

405nm, 8mW, 1400mA, SMA Connector,  
Fiber-Coupled LED

ALL DIMS IN

mm

DWG NO

23728

SHEET  
2 OF 18