


TECHSPEC® Ultrafast Broadband Mirrors


385 - 415nm Reflectance
FOR REFERENCE ONLY



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

TECHSPEC® Ultrafast Broadband Mirrors


385-415nm GDD Performance
FOR REFERENCE ONLY



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

TECHSPEC® Ultrafast Broadband Mirrors


770 - 830nm Reflectance
FOR REFERENCE ONLY



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED

TECHSPEC® Ultrafast Broadband Mirrors

770 - 830nm GDD Performance
FOR REFERENCE ONLY



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED