





- NOTES:
- 1. SUBSTRATE MATERIAL: N-BK7
  - 2. ROHS COMPLIANT
  - 3. COATING (APPLY ACROSS CLEAR APERTURE)
    - S1: NONE
    - S2: Ravg >98% @ 450 - 2000nm
    - Ravg >98% @ 2000 - 10000nm

4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 <b>Edmund Optics®</b>			
SHAPE	PLANO	PLANO				
ANGEL TOL. (arcmin)	±2	±2		TITLE		
SURFACE QUALITY	40-20	40-20		6.25mm, Protected Silver Coated, N-BK7 90° Specialty Mirror		
SURFACE FLATNESS	λ/4	λ/4				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	25-699
					SHEET 14 OF 31	