




- NOTES:
- 1. SUBSTRATE: Polymer Film CP42HE
  - 2. WAVELENGTH RANGE: 400 - 700 nm
  - 3. POLARIZATION EFFICIENCY (%): >99.90
  - 4. TRANSMISSION (%):  
SINGLE: 42.00
  - 7. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                                                                                                              |    |                                                                                                      |       |               |
|--------------------------------------------------------------------------------------------------------------|----|------------------------------------------------------------------------------------------------------|-------|---------------|
| THIRD ANGLE PROJECTION  |    |  Edmund Optics® |       |               |
| TITLE                                                                                                        |    | 100 x 100mm Left-Handed Circular Polarizing Film (CP42HE)                                            |       |               |
| ALL DIMS IN                                                                                                  | mm | DWG NO                                                                                               | 29442 | SHEET 5 OF 50 |