



NOTES:

- 1. SUBSTRATE:
FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <3 ARCmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
S1: R(abs) S & P > 99.80% @ 400nm @ 0-45° AOI
- S2: NONE
- 4. FINE GRIND SURFACE
- 5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY
ACROSS CLEAR APERTURE
- 6. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACES



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	Edmund Optics®				
SHAPE	PLANO	PLANO					
SURFACE QUALITY	10 - 5	COMMERCIAL POLISH	THIRD ANGLE PROJECTION				
SURFACE FLATNESS	λ/10	N/A					
CLEAR APERTURE	Ø 22.86	N/A					
COATING APERTURE	Ø 22.86	N/A					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					
			ALL DIMS IN	mm	DWG NO	28990	SHEET 49 OF 86