




NOTES:


- 1. CUT-ON WAVELENGTH: 475±9.5nm
- 2. BLOCKING RANGE: 491.7 - 546.7nm
- 3. TRANSMISSION RANGE: >85% @ 400 - 458.5nm
- 4. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

EO® **Edmund Optics®**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

THIRD ANGLE PROJECTION 		TITLE	475nm 12.45mm, Ultra-Thin OD 4.0 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	29199	SHEET 13 OF 24