



NOTES:

- 1. SUBSTRATE:
SAPPHIRE (AL2O3)
- 2. SURFACE S2 TO BE PARALLEL WITH SUFACE S1 TO WITHIN ≤ 3.5 ARMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: R(AVG)<0.5% @ 350 - 700nm


4. FINE GRIND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<div><div><div>THIRD ANGLE PROJECTION</div></div><div>ALL DIMS INmm</div></div> <div><div><div>Edmund Optics®</div><div>20mm Dia., 0.5mm Thick, VIS-EXT AR Coated Sapphire Window</div></div><div><div>DWG NO28564</div><div>SHEET20 OF 41</div></div></div>
SHAPE	PLANO	PLANO	
CLEAR APERTURE	Ø 18.00	Ø 18.00	
SURFACE FLATNESS	2λ	2λ	
SURFACE QUALITY	80-50	80-50	
BIREFRINGENCE (no-ne)	0.008	0.008	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	